www.koolance.com

Specifications Sheet

Generated: 2026-10-26

P/N: COV-TKTOPX70


Reservoir Top with Fill Port (80mm OD)




Acetal reservoir top for Koolance 80mm OD reservoir bodies. Nickel-plated brass, G 1/4 BSPP (parallel) thread top fill port. Hex mounting nut and insulating washer included.

General	
Weight	0.20 lb (0.09 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	2kgf/cm2 (28.5psi)
Max Temperature Tolerance	80°C (176°F)

File





NO.	DESCRIPTION				MATER'L		QUANTITY	REMARKS
KOOLANCE					UNIT	MM	APPAR	COV-TKTOPX70
	BY	BY	BY	APPRO BY	SCALE	N/S	TITLE	Ass'y
DATE					3RD ANGLE			
04/10/2017	S.J.LEE				CODE NO.		DWG. NO.	