www.koolance.com

Specifications Sheet

Generated: 2026-11-13

P/N: SEN-TPL010K


Coolant Temperature Sensor Inline, Female/Female Threads, 10K Ohm




Coolant thermistor temperature sensor within nickel-plated brass body. G 1/4 BSPP threads are provided on both sides. Wire length = 30" (76cm). NOTE: This sensor will only work with Koolance products which use 10K Ohm @25°C sensors (first introduced in 2011).

General	
Weight	0.13 lb (0.06 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	20kgf/cm2 (284.5psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	Brass, Nickel

File





SECTION A-A

NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	ITEM SEN-TPL010K	
	BY	BY	BY	APPRD BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
12.17.2021	YS.SHIN				CODE NO.	DWG. NO.	PAGE