



Flat thermistor temperature sensor compatible with Koolance multi-sensor systems. Wire length = 30" (76cm).

This type of thermistor is more fragile than metal-encased plug versions. The sensor may burn out if placed in direct contact with a high heat source. The probe should also *not* be placed directly between a heat source and its liquid cooler to prevent inadequate heat transfer.

NOTE: This sensor will only work with Koolance products which use 10K Ohm @25°C sensors (first introduced in 2011).

General	
Weight	0.01 lb (0.00 kg)
Max Temperature Tolerance	90°C (194°F)