

Koolance blue PVC tubing with 10mm (3/8in) internal diameter, 13mm (1/2in) external diameter. Bend radius is approximately 37mm (1.5in). This tubing is one roll of 100m (328ft).



General	
Weight	15.40 lb (6.99 kg)
Max Pressure Tolerance @ 25° C	5kgf/cm ² (71psi)
Max Temperature Tolerance	70° C (158° F)
Hardness (Shore)	80A