



www.koolance.com

**Specifications Sheet**

Generated: 2025-09-02

**P/N: HOS-10BU-100M**

**Tubing Roll, PVC Blue, Dia: 10mm x 13mm  
(3/8in x 1/2in) - [Length 100m / 328ft]**



Koolance blue PVC tubing with 10mm (3/8in) internal diameter, 13mm (1/2in) external diameter. Bend radius is approximately 37mm (1.5in). This tubing is one roll of 100m (328ft).

General	
Weight	15.40 lb (6.99 kg)
Max Pressure Tolerance @ 25°C	5kgf/cm2 (71psi)
Max Temperature Tolerance	70°C (158°F)
Hardness (Shore)	80A