

**Tubing Roll, PVC Blue, Dia: 10mm x 13mm  
(3/8in x 1/2in) - [Length 100m / 328ft]**

Koolance blue PVC tubing with 10mm (3/8in) internal diameter, 13mm (1/2in) external diameter. Bend radius is approximately 37mm (1.5in). This tubing is one roll of 100m (328ft).



<b>General</b>	
Weight	15.40 lb (6.99 kg)
Max Pressure Tolerance @ 25° C	5kgf/cm <sup>2</sup> (71psi)
Max Temperature Tolerance	70° C (158° F)
Hardness (Shore)	80A