

P/N: HOS-13BU-100M

**Tubing Roll, PVC Blue, Dia: 13mm x 16mm
(1/2in x 5/8in) - [Length 100m / 328ft]**

Koolance blue PVC tubing with 13mm (1/2in) internal diameter, 16mm (5/8in) external diameter. Bend radius is approximately 55mm (2.2in). This tubing is one roll of 100m (328ft).



General	
Weight	15.40 lb (6.99 kg)
Max Pressure Tolerance @ 25°C	4kgf/cm ² (57psi)
Max Temperature Tolerance	70°C (158°F)
Hardness (Shore)	75A