www.koolance.com

Specifications Sheet

Generated: 2026-11-04

P/N: HOS-10X13PU-CL-3M


Tubing, PU Clear, Dia: 10mm x 13mm (3/8in x 1/2in) - [Length 3m / 9.8ft]




Koolance clear polyurethane tubing with 10mm (3/8in) internal diameter, 13mm (1/2in) external diameter. Length 3m / 9.8ft. Bend radius is approximately 42mm (1.7in).

General	
Weight	0.80 lb (0.36 kg)
Max Pressure Tolerance @ 25°C	6kgf/cm2 (85psi)
Max Temperature Tolerance	80°C (176°F)
Hardness (Shore)	85A

File





Clear polyurethane

NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT inch	APPAR	
	BY	BY	BY	APPRD BY	SCALE N/S	TITLE HOS-10X13PU-CL-XX	
DATE					3RD ANGLE		
2026.05.11	SK.An				CODE NO.	DWG. NO.	