www.koolance.com

Specifications Sheet

Generated: 2026-11-20

P/N: HOS-06X10PU-CL-100M


Tubing Roll, PU Clear, Dia: 06mm x 10mm (1/4in x 3/8in) - [Length 100m / 328ft]




Koolance clear polyurethane tubing with 6mm (1/4in) internal diameter, 10mm (3/8in) external diameter. Bend radius is approximately 25mm (0.98in). This tubing is one roll of 100m (328ft).

General	
Weight	9.80 lb (4.45 kg)
Max Pressure Tolerance @ 25°C	7kgf/cm2 (99.6psi)
Max Temperature Tolerance	80°C (176°F)
Hardness (Shore)	85A

File





Clear polyurethane

NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT inch	APPAR	
	BY	BY	BY	APPRD BY	SCALE N/S	TITLE HOS-06X10PU-CL-XX	
DATE					3RD ANGLE		
2026.05.11	SK.An				CODE NO.	DWG. NO.	