



www.koolance.com

## Specifications Sheet

Generated: 2024-03-25

# P/N: HOS-10CL-15M

**Tubing, PVC Clear, Dia: 10mm x 13mm (3/8in x 1/2in) - [Length 15m / 49.2ft]**



Koolance clear PVC tubing with 10mm (3/8in) internal diameter, 13mm (1/2in) external diameter. Length 15m / 49.2ft. Bend radius is approximately 37mm (1.5in).

| General                       |                   |
|-------------------------------|-------------------|
| Weight                        | 2.80 lb (1.27 kg) |
| Max Pressure Tolerance @ 25°C | 5kgf/cm2 (71psi)  |
| Max Temperature Tolerance     | 70°C (158°F)      |
| Hardness (Shore)              | 80A               |