



Koolance clear PVC tubing with 10mm (3/8in) internal diameter, 13mm (1/2in) external diameter. Bend radius is approximately 37mm (1.5in). This tubing is one roll of 100m (328ft).

General	
Weight	15.40 lb (6.99 kg)
Max Pressure Tolerance @ 25°C	5kgf/cm ² (71psi)
Max Temperature Tolerance	70°C (158°F)
Hardness (Shore)	80A