www.koolance.com

Specifications Sheet

Generated: 2026-11-10


P/N: HOS-13CL-15M


Tubing, PVC Clear, Dia: 13mm x 16mm (1/2in x 5/8in) - [Length 15m / 49.2ft]



Koolance clear PVC tubing with 13mm (1/2in) internal diameter, 16mm (5/8in) external diameter. Length 15m / 49.2ft. Bend radius is approximately 55mm (2.2in).

General	
Weight	4.00 lb (1.81 kg)
Max Pressure Tolerance @ 25°C	4kgf/cm2 (57psi)
Max Temperature Tolerance	70°C (158°F)
Hardness (Shore)	75A





Clear PVC

NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT inch	APPAR	
	BY	BY	BY	APPRD BY	SCALE N/S	TITLE HOS-13CL-XX	
DATE					3RD ANGLE		
2026.05.11	SK.An				CODE NO.	DWG. NO.	