



Koolance clear PVC tubing with 13mm (1/2in) internal diameter, 16mm (5/8in) external diameter. Length 15m / 49.2ft. Bend radius is approximately 55mm (2.2in).

General	
Weight	4.00 lb (1.81 kg)
Max Pressure Tolerance @ 25°C	4kgf/cm ² (57psi)
Max Temperature Tolerance	70°C (158°F)
Hardness (Shore)	75A