

Tubing, PVC Clear, Dia: 13mm x 16mm (1/2in x 5/8in) - [Length 3m / 9.8ft]

Koolance clear PVC with 13mm (1/2in) internal diameter, 16mm (5/8in) external diameter. Length 3m / 9.8ft. Bend radius is approximately 55mm (2.2in).



General	
Weight	0.80 lb (0.36 kg)
Max Pressure Tolerance @ 25°C	4kgf/cm ² (57psi)
Max Temp. Operating Tolerance	70°C (158°F)
Hardness (Shore)	75A