

Tubing, PVC Clear, Dia: 06mm x 10mm (1/4in x 3/8in) - [Length 15m / 49.2ft]



Koolance clear PVC tubing with 6mm (1/4in) internal diameter, 10mm (3/8in) external diameter. Length 15m / 49.2ft. Bend radius is approximately 22mm (0.9in).

General	
Weight	1.75 lb (0.79 kg)
Max Pressure Tolerance @ 25°C	6kgf/cm ² (64psi)
Max Temperature Tolerance	70°C (158°F)
Hardness (Shore)	80A