

Tubing, PVC Clear, Dia: 06mm x 10mm (1/4in x 3/8in) - [Length 3m / 9.8ft]



Koolance clear PVC tubing with 6mm (1/4in) internal diameter, 10mm (3/8in) external diameter. Length 3m / 9.8ft. Bend radius is approximately 22mm (0.9in).

General	
Weight	0.50 lb (0.23 kg)
Max Pressure Tolerance @ 25 °C	6kgf/cm2 (64psi)
Max Temperature Tolerance	70 °C (158 °F)
Hardness (Shore)	80A