



Koolance clear PVC tubing with 6mm (1/4in) internal diameter, 10mm (3/8in) external diameter. Length 100m / 328ft. Bend radius is approximately 22mm (0.9in).

General	
Weight	20.00 lb (9.07 kg)
Max Pressure Tolerance @ 25°C	6kgf/cm ² (64psi)
Max Temperature Tolerance	70°C (158°F)
Hardness (Shore)	80A