www.koolance.com

**Specifications Sheet**

Generated: 2026-11-15

# P/N: HOS-06CL-100M


## Tubing Roll, PVC Clear, Dia: 06mm x 10mm (1/4in x 3/8in) - [Length 100m / 328ft]





Koolance clear PVC tubing with 6mm (1/4in) internal diameter, 10mm (3/8in) external diameter. Length 100m / 328ft. Bend radius is approximately 22mm (0.9in).

| General | |
|---|---|
| Weight | 20.00 lb (9.07 kg) |
| Max Pressure Tolerance @ 25°C | 6kgf/cm2 (64psi) |
| Max Temperature Tolerance | 70°C (158°F) |
| Hardness (Shore) | 80A |

File




Clear PVC

| NO. | DESCRIPTION | | | | MATER'L | QUANTITY | REMARKS |
|---|---|---|---|---|---|---|---|
| KOOLANCE | | | | | UNIT inch | APPAR | |
| | BY | BY | BY | APPRD BY | SCALE N/S | TITLE HOS-06CL-XX | |
| DATE | | | | | 3RD ANGLE | | |
| 2026.05.11 | SK.An | | | | CODE NO. | DWG. NO. | |