

**Tubing, PVC Green, Dia: 10mm x 13mm (3/8in
x 1/2in), Ea: 305mm (1ft)**

Koolance green PVC tubing with 10mm (3/8in) internal diameter, 13mm (1/2in) external diameter. Bend radius is approximately 37mm (1.5in). This tubing is priced per foot (305mm) and will be cut to the ordered length.



| General | |
|-------------------------------|-------------------------------|
| Weight | 0.06 lb (0.03 kg) |
| Max Pressure Tolerance @ 25°C | 5kgf/cm ² (71 psi) |
| Max Temperature Tolerance | 70°C (158°F) |
| Hardness (Shore) | 80A |