www.koolance.com

Specifications Sheet

Generated: 2026-11-09

P/N: HOS-10GN

Tubing, PVC Green, Dia: 10mm x 13mm (3/8in x 1/2in), Ea: 305mm (1ft)



Koolance green PVC tubing with 10mm (3/8in) internal diameter, 13mm (1/2in) external diameter. Bend radius is approximately 37mm (1.5in). This tubing is priced per foot (305mm) and will be cut to the ordered length.

General	
Weight	0.06 lb (0.03 kg)
Max Pressure Tolerance @ 25°C	5kgf/cm2 (71psi)
Max Temperature Tolerance	70°C (158°F)
Hardness (Shore)	80A