

P/N: HOS-13GN-100M**Tubing Roll, PVC Green, Dia: 13mm x 16mm
(1/2in x 5/8in) - [Length 100m / 328ft]**

Koolance green PVC tubing with 13mm (1/2in) internal diameter, 16mm (5/8in) external diameter. Bend radius is approximately 55mm (2.2in). This tubing is one roll of 100m (328ft).

General	
Weight	20.40 lb (9.25 kg)
Max Pressure Tolerance @ 25°C	4kgf/cm ² (57psi)
Max Temperature Tolerance	70°C (158°F)
Hardness (Shore)	75A