

**Tubing, PVC Green, Dia: 13mm x 16mm (1/2in  
x 5/8in), Ea: 305mm (1ft)**

Koolance green PVC tubing with 13mm (1/2in) internal diameter, 16mm (5/8in) external diameter. Bend radius is approximately 55mm (2.2in). This tubing is priced per foot (305mm) and will be cut to the ordered length.



<b>General</b>	
Weight	0.09 lb (0.04 kg)
Max Pressure Tolerance @ 25°C	4kgf/cm <sup>2</sup> (57psi)
Max Temperature Tolerance	70°C (158°F)
Hardness (Shore)	75A