

**Tubing, PVC Green, Dia: 13mm x 16mm (1/2in
x 5/8in), Ea: 305mm (1ft)**

Koolance green PVC tubing with 13mm (1/2in) internal diameter, 16mm (5/8in) external diameter. Bend radius is approximately 55mm (2.2in). This tubing is priced per foot (305mm) and will be cut to the ordered length.



General	
Weight	0.09 lb (0.04 kg)
Max Pressure Tolerance @ 25°C	4kgf/cm ² (57psi)
Max Temperature Tolerance	70°C (158°F)
Hardness (Shore)	75A