

**Tubing Roll, PVC Silver, Dia: 13mm x 16mm  
(1/2in x 5/8in), Ea: 100m (328ft)**

Koolance silver PVC tubing with 13mm (1/2in) internal diameter, 16mm (5/8in) external diameter. Bend radius is approximately 55mm (2.2in). This tubing is one roll of 100m (328ft).



General	
Weight	20.40 lb (9.25 kg)
Max Pressure Tolerance @ 25° C	4kgf/cm <sup>2</sup> (57psi)
Max Temperature Tolerance	70° C (158° F)
Hardness (Shore)	75A