

**Tubing, PVC Silver, Dia: 13mm x 16mm (1/2in x 5/8in), Ea: 305mm (1ft)**

Koolance silver PVC tubing with 13mm (1/2in) internal diameter, 16mm (5/8in) external diameter. Bend radius is approximately 55mm (2.2in). This tubing is priced per foot (305mm) and will be cut to the ordered length.



| <b>General</b>                |                              |
|-------------------------------|------------------------------|
| Weight                        | 0.09 lb (0.04 kg)            |
| Max Pressure Tolerance @ 25°C | 4kgf/cm <sup>2</sup> (57psi) |
| Max Temperature Tolerance     | 70°C (158°F)                 |
| Hardness (Shore)              | 75A                          |