



www.koolance.com

Specifications Sheet

Generated: 2025-08-24

P/N: HOS-13SL

Tubing, PVC Silver, Dia: 13mm x 16mm (1/2in x 5/8in), Ea: 305mm (1ft)

Koolance silver PVC tubing with 13mm (1/2in) internal diameter, 16mm (5/8in) external diameter. Bend radius is approximately 55mm (2.2in). This tubing is priced per foot (305mm) and will be cut to the ordered length.



| General | |
|--------------------------------|-------------------|
| Weight | 0.09 lb (0.04 kg) |
| Max Pressure Tolerance @ 25 °C | 4kgf/cm2 (57psi) |
| Max Temperature Tolerance | 70 °C (158 °F) |
| Hardness (Shore) | 75A |