


VL2 Quick Disconnect Low-Spill Coupling, Male Panel Barb for ID 10mm (3/8in)




Koolance patented quick disconnect coupling with automatic shutoff. 10mm (3/8in) ID male panel-mountable hose barb with clamp. It will only fit a Koolance VL2 female quick disconnect.

After a quarter twist, the quick-disconnect fittings will separate. Liquid on both sides will be automatically obstructed with only 0.5-1mL freed.

General	
Weight	0.07 lb (0.03 kg)



VL2 QDC Nozzle (Straight Male/Female Connection)



Koolance “VL2” 6mm or 10mm ID
Panel Barb Hole Size

