

## VL3N Male Quick Disconnect No-Spill Coupling, Panel, Female Threaded G 1/4



Koolance patented quick disconnect no-spill coupling with automatic shutoff. G 1/4 BSPP (parallel) thread female with panel-mount opposite a male "VL3N" quick-disconnect. It will only fit a Koolance VL3N female quick disconnect.

After a quarter twist, the quick-disconnect fittings will separate. Liquid on both sides will be automatically obstructed with approximately 0.2ml freed. Coolant volume lost upon disconnection will rise with internal pressure higher than 0.5kgf/cm<sup>2</sup> (7psi). Fittings are nickel-plated brass, EPDM o-rings. Maximum operating pressure is 6kgf/cm<sup>2</sup> (85 psi). Maximum operating temperature is 90° C.

### General

Weight	0.09 lb (0.04 kg)
--------	-------------------

No-Spill Shut-Off Valve

