

VL3N Male Quick Disconnect No-Spill Coupling, Panel, Female Threaded G 1/4



Koolance patented quick disconnect no-spill coupling with automatic shutoff. G 1/4 BSPP (parallel) thread female with panel-mount opposite a male "VL3N" quick-disconnect. It will only fit a Koolance VL3N female quick disconnect.

After a quarter twist, the quick-disconnect fittings will separate. Liquid on both sides will be automatically obstructed with approximately 0.2ml freed. Coolant volume lost upon disconnection will rise with internal pressure higher than 0.5kgf/cm² (7psi). Fittings are nickel-plated brass, EPDM o-rings. Maximum operating pressure is 6kgf/cm² (85 psi). Maximum operating temperature is 90° C.

General	
Weight	0.09 lb (0.04 kg)

No-Spill Shut-Off Valve

