

VL4N Female Quick Disconnect No-Spill Coupling,, Barb for ID 16mm (5/8in)



Koolance patented quick disconnect no-spill coupling with automatic shutoff. 16mm (5/8in) ID female with hose barb and clamp. It will only fit a Koolance VL4N male quick disconnect.

After a quarter twist, the quick-disconnect fittings will separate. Liquid on both sides will be automatically obstructed with approximately 0.2ml freed. Coolant volume lost upon disconnection will rise with internal pressure higher than 0.5kgf/cm² (7psi). Maximum operating pressure is 5kgf/cm² (71 psi). Maximum operating temperature is 90°C.

General

Weight	0.26 lb (0.12 kg)
--------	-------------------

No-Spill Shut-Off Valve

