








Manual ball valve for closing, opening, or partially restricting coolant flow. Nickel-plated brass, G 1/4 BSPP threading.

General	
Weight	0.19 lb (0.09 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	10kgf/cm2 (142.2psi)
Max Temperature Tolerance	100° C (212° F)



NO.	DESCRIPTION				MATER'L		QUANTITY	REMARKS		
 KOOLANCE®					UNIT	MM	ITEM VLV-BL1X2			
					SCALE	N/S	TITLE			
	BY	BY	BY	APPRO BY	3RD ANGLE		Ass'y			
DATE										
	S.J.LEE				CODE NO.		DWG. NO.			PAGE

[illegible]