







Inline drain valve to expedite coolant evacuation without turning your unit upside-down. This product is designed to be placed inline on any hose. Simply choose fittings for the desired hose diameter. Construction is nickle-plated brass.

To use, install the valve on a hose near the bottom of your setup. When you need to empty the system, place a container below the valve and unscrew it. A segment of 6mm (1/4in) ID tubing can be attached to the drain nozzle. Next, open the top reservoir refill plug on your cooling system.

General	
Weight	0.23 lb (0.10 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120° C (248° F)
Wetted Materials	Nickel-Plated Brass, EPDM



NO.		DESCRIPTION		MATER'L		QUANTITY	REMARKS
 KOOLANCE®		UNIT		MM	ITEM VLV-XUTX4B		
		SCALE		N/S	TITLE		
					Ass'y		
DATE	BY	BY	BY	APPRO	BY	3RD ANGLE	
	S.J.LEE					CODE NO.	DWG. NO.
							PAGE

[illegible]