www.koolance.com

Specifications Sheet

Generated: 2026-11-19

P/N: SPL-YF2MS1G4


Y-Splitter, Dual Female, Single Swivel Male G 1/4 BSPP



Koolance "Y-shape" tubing splitter with one swiveling male and two female G 1/4 BSPP threads. Made of nickel-plated brass with EPDM o-rings.

General	
Weight	0.10 lb (0.05 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	120°C (248°F)

File



NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	APPAR SPL-YF2MS1G4	
	BY	BY	BY	APPRO BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
JAN.14.2021	S.J.LEE				CODE NO.	DWG. NO.	