




Koolance "Y-shape" tubing splitter with one swiveling male and two female G 1/4 BSPP threads. Made of nickel-plated brass with EPDM o-rings.

General	
Weight	0.10 lb (0.05 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	120°C (248°F)



NO.	DESCRIPTION	MATER'L		QUANTITY	REMARKS
	KOOLANCE®	UNIT	MM	APPAR	SPL-YF2MS1G4
		SCALE	N/S	TITLE	
DATE	BY	BY	BY	BY	Ass'y
JAN.14.2021	S.J.LEE				
					3RD ANGLE
					CODE NO.
					DWG. NO.