www.koolance.com

**Specifications Sheet**

Generated: 2026-10-27

# P/N: SPL-YF3G4-BK


## Y-Splitter, Triple Female G 1/4 BSPP, *Black*




Koolance "Y-shape" tubing splitter with three female G 1/4 BSPP threads. Made of brass.

| General | |
|---|---|
| Weight | 0.10 lb (0.05 kg) |
| Fitting Thread | G 1/4 BSPP |
| Max Pressure Tolerance @ 25°C | 15kgf/cm2 (213.4psi) |
| Max Temperature Tolerance | 120°C (248°F) |

File




| NO. | DESCRIPTION | | | | MATER'L | QUANTITY | REMARKS |
|---|---|---|---|---|---|---|---|
| KOOLANCE | | | | | UNIT MM | APPAR SPL-YF3G4 | |
| | BY | BY | BY | APPRO BY | SCALE N/S | TITLE Ass'y | |
| DATE | | | | | 3RD ANGLE | | |
| JAN.14.2021 | S.J.LEE | | | | CODE NO. | DWG. NO. | |