www.koolance.com | (Address) Koolance Bld, 40, Deokcheon-ro 34, Manan-gu, Anyang-si, Gyeonggi-do, 14088, South Korea | (Phone) +82-31-448-6183

Declaration of RoHS 3 Compliance

Koolance Product P/N: EX2-1055
Date: 2024-03-29

The products listed above do not contain any of the following restricted substances above the limits listed below, and are therefore compliant with European Directive 2015/863/EU (RoHS):

Heavy Metals	Maximum Concentration Per Homogeneous Material Level (ppm)
Lead*	1000
Mercury	1000
Hexavalent Chromium	1000
Cadmium	100

Exemption: *6c) Lead as an alloying element in copper containing up to 4% lead by weight.

Flame Retardants	Maximum Concentration Per Homogeneous Material Level (ppm)
PBB	1000
PBDE**	1000

Note: **The above products do NOT use the exemption "9a) DecaBDE in polymeric applications".

Phthalates	Maximum Concentration Per Homogeneous Material Level (ppm)
BBP (Butyl benzyl Phthalate)	1000
DBP (Dibutyl Phthalate)	1000
DEHP (Di-EthyHexvl Phthalate)	1000
DIBP (Diisobutyl Phthalate)	1000



By:
Name: Steve Seo
Koolance Korea Quality Control