www.koolance.com | (Address) Koolance Bld, 40, Deokcheon-ro 34, Manan-gu, Anyang-si, Gyeonggi-do, 14088, South Korea | (Phone) +82-31-448-6183

# Declaration of RoHS 3 Compliance

**Koolance Product P/N:** SEN-AP008G
**Date:** 2024-03-28

The products listed above do not contain any of the following restricted substances above the limits listed below, and are therefore compliant with European Directive 2015/863/EU (RoHS):

| Heavy Metals | Maximum Concentration Per Homogeneous Material Level (ppm) |
|---|---|
| Lead* | 1000 |
| Mercury | 1000 |
| Hexavalent Chromium | 1000 |
| Cadmium | 100 |

**Exemption:** *6c) Lead as an alloying element in copper containing up to 4% lead by weight.

| Flame Retardants | Maximum Concentration Per Homogeneous Material Level (ppm) |
|---|---|
| PBB | 1000 |
| PBDE** | 1000 |

**Note:** **The above products do NOT use the exemption "9a) DecaBDE in polymeric applications".

| Phthalates | Maximum Concentration Per Homogeneous Material Level (ppm) |
|---|---|
| BBP (Butyl benzyl Phthalate) | 1000 |
| DBP (Dibutyl Phthalate) | 1000 |
| DEHP (Di-EthyHexvl Phthalate) | 1000 |
| DIBP (Diisobutyl Phthalate) | 1000 |



By:
Name: Steve Seo
Koolance Korea Quality Control