www.koolance.com

Specifications Sheet

Generated: 2026-11-19

P/N: FIT-V10X16N14

Compression Fitting for 10mm x 16mm (3/8in x 5/8in), 1/4 NPT



Single fitting for 3/8in (10mm) ID, 5/8in (16mm) OD tubing.
1/4 NPT (tapered) thread.

General	
Weight	0.15 lb (0.07 kg)
Max Pressure Tolerance @ 25°C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	Brass, Nickel Plating, EPDM

File



REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY

REVISION

NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE INC.		UNIT MM	APPAR FIT-V10X16N14	
	BY BY BY APPRD BY	SCALE N/S	TITLE Ass'y	
DATE		3RD ANGLE		
	S.J.LEE	REF. NO.	DWG. NO.	