www.koolance.com

Specifications Sheet

Generated: 2026-11-17

P/N: VL4-M16-19S

VL4 Quick Disconnect Low-Spill Coupling, Male for 16mm x 19mm (5/8in x 3/4in)



Koolance patented quick disconnect coupling with automatic shutoff. 16mm (5/8in) ID, 19mm (3/4in) OD male straight connection with compression fitting. It will only fit a Koolance VL4 female quick disconnect.

After a quarter twist, the quick-disconnect fittings will separate. Liquid on both sides will be automatically obstructed with only 0.5-1mL freed.

General	
Weight	0.16 lb (0.07 kg)




47.4
Ø18.2
Ø18.5
Ø25.0