www.koolance.com

Specifications Sheet

Generated: 2026-11-23

P/N: VL4N-F16-19B

VL4N Female Quick Disconnect No-Spill Coupling,, Barb for ID 16mm (5/8in)



Koolance patented quick disconnect no-spill coupling with automatic shutoff. 16mm (5/8in) ID female with barb fitting and clamp. It will only fit a Koolance VL4N male quick disconnect.

After a quarter twist, the quick-disconnect fittings will separate. Liquid on both sides will be automatically obstructed with approximately 0.2ml freed. Coolant volume lost upon disconnection will rise with internal pressure higher than 0.5kgf/cm2 (7psi). Maximum operating pressure is 5kgf/cm2 (71 psi). Maximum operating temperature is 90°C.

General	
Weight	0.26 lb (0.12 kg)



