

PLT-UN40F Cold Plate, 40mm x 40mm (1.57in x 1.57in)




PLT-UN40F is a high-efficiency, general-purpose cold plate for thermal applications such as TEC, LED, image sensor, and semiconductor cooling. The cooling area footprint is 40mm x 40mm (1.57in x 1.57in), and it utilizes a 0.5mm microfin internal structure.


One loose steel bracket is included, designed for easy fabrication and modification (see dimensions under the "Files" tab). The included bracket accommodates diagonal mounting hole distances from approximately 60mm to 88mm (2.36in to 3.46in).

Cold plate materials include copper, a brass top, anti-corrosive nickel plating, and EPDM o-ring. Threaded for G 1/4 BSPP fittings.


Cold Plates	
Flow Resistance @ 5LPM (10-13mm ID)	0.07 kgf/cm ² (1.0psi)
Thermal Resistance @ 5LPM (Approx.)	0.044° C/W
General	
Weight	0.34 lb (0.15 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	8kgf/cm ² (113.8psi)
Max Temperature Tolerance	100° C (212° F)
Wetted Materials	Nickel-Plated Copper, Nickel-Plated Brass, EPDM






PLT-UN40F



PLT-UNxxF





REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY

NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KODANCE INC.				UNIT	MM	ITEM	PLT-UN40F
				SCALE	N/S	TITLE	Ass'y
DATE	BY	BY	BY	APPRO	BY	3RD ANGLE	
	S.J.LEE					CODE NO.	DWG. NO. PAGE