





## Radiator, 3x120mm Fans, 54mm Thick, 30-FPI Copper




HX-360XC is an extra thick (54mm, 2.1in) copper core radiator with a fin density of 30 FPI (fins per inch). It offers greatest performance when sandwiched between multiple high speed 120mm fans. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans on one side only (see Koolance [radiator screw packs](#) for additional options).


General	
Weight	3.50 lb (1.59 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	1.5kgf/cm2 (21psi)
Max Temperature Tolerance	150°C (302°F)
Wetted Materials	Brass/Copper
Radiators	
Fan Capacity	3 x 120mm
Fins Per Inch (FPI)	30






10-13mm ID Tubing





REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
REVISION					

NO.		DESCRIPTION				MATER'L		QUANTITY	REMARKS	
		 <b>KOOLANCE®</b>				UNIT	MM	ITEM HX-360XC		
						SCALE	N/S	TITLE		
		BY	BY	BY	APPRO BY	3RD ANGLE			Ass'y	
DATE										
		S.J.LEE				CODE NO.		DWG. NO.		PAGE