









HX-CU420V is a low profile copper core radiator designed for one 120mm fan. With a fin density of 30 FPI (fins per inch), it offers best performance with higher air flow. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).

General	
Weight	0.80 lb (0.36 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	1.5kgf/cm2 (21psi)
Max Temperature Tolerance	150° C (302° F)
Wetted Materials	Brass/Copper
Radiators	
Fan Capacity	1 x 120mm
Fins Per Inch (FPI)	30










REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
REVISION					

NO.		DESCRIPTION		MATER'L		QUANTITY	REMARKS
		UNIT		MM	ITEM HX-CU420V		
		SCALE		N/S	TITLE Ass'y		
		3RD ANGLE					
DATE		BY	BY	BY	BY	CODE NO.	
S.J.LEE						DWG. NO.	
						PAGE	