








HX-720 is a low profile aluminum radiator designed for two 120mm fans. With a fin density of 18 FPI (fins per inch), it is optimized for quieter air flow ranges. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).

General	
Weight	2.60 lb (1.18 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	20kgf/cm2 (284.5psi)
Max Temperature Tolerance	200° C (392° F)
Wetted Materials	Aluminum
Radiators	
Fan Capacity	2 x 120mm
Fins Per Inch (FPI)	18







NO.		DESCRIPTION				MATER'L		QUANTITY	REMARKS
<b>KOOLANCE</b> INC.		UNIT		MM		SCALE		ITEM	HX-720
		BY		BY		BY		TITLE	
DATE		BY		BY		BY		3RD ANGLE	
S.J.LEE								CODE NO.	
								DWG. NO.	
								PAGE	