









HX-CU1320V is a low profile copper core radiator designed for four 120mm fans. With a fin density of 30 FPI (fins per inch), it offers best performance with higher air flow. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).


General	
Weight	2.70 lb (1.22 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	1.5kgf/cm2 (21psi)
Max Temperature Tolerance	150° C (302° F)
Wetted Materials	Brass/Copper
Radiators	
Fan Capacity	4 x 120mm
Fins Per Inch (FPI)	30









NO.		DESCRIPTION				MATER'L		QUANTITY	REMARKS
 KOOLANCE®						UNIT	MM	ITEM HX-CU1320V	
						SCALE	N/S	TITLE Ass'y	
		BY	BY	BY	APPRO	BY			
DATE							3RD ANGLE		
		S.J.LEE				CODE NO.		DWG. NO.	
								PAGE	

REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
REVISION					