

**QD2 Female Quick Disconnect No-Spill
Coupling, Male Threaded G 1/4 BSPP**





Koolance patented quick disconnect no-spill coupling with automatic shutoff. G 1/4 BSPP (parallel) thread male fitting for screwing directly into a water block or other component. It will only fit a Koolance QD2 male quick disconnect.

After pulling the ring on the female QDC side, the quick-disconnect fittings will separate. Liquid on both sides will be automatically obstructed with approximately 0.2ml freed. Coolant volume lost upon disconnection will rise with internal pressure higher than 0.5kgf/cm² (7psi).


General	
Weight	0.08 lb (0.04 kg)
Max No-Spill Pressure	0.5kgf/cm ² (7psi)
Max Pressure Tolerance @ 25 °C	8kgf/cm ² (113.8psi) connected, 5kgf/cm ² (71psi) disconnected
Max Temperature Tolerance	80 °C (176 °F)
Min Pressure Tolerance @ 25 °C	-1.0kgf/cm ² (-14psi)
Min Storage Temperature (*No Freezing)	-20°C (-4°F)
Seal Material	EPDM (Water/Glycol Liquids)
Wetted Materials	Nickel-Plated Brass, Stainless Steel, EPDM

QD2 (One Pair)





REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY	
REVISION						

NO.		DISCRIPTION				MATER'L		QUANTITY	REMARKS		
		DECIMAL PLACES	INCHES	MILLIMETRES	UNIT	MM	ITEM QD2				
		.XXX	±.005	±0.1	SCALE	N/S	TITLE QD2-FG4				
		.XX	±.010	±0.3							
		.X	±.020	±0.5	3RD ANGLE						
DATE		ANGULAR DIMENSIONS				CODE NO.		DWG. NO.			
		XX°	±0.5°								
		XX.X°	±0.1°								
		SURFACE	SURFACE	SURFACE							
		ROUGHNESS	.63	1.6							
		SONG									
				</							