

**PLT-UN45P Cold Plate, 45mm x 45mm (1.8in x 1.8in) (Refurb)**



PLT-UN45F is a general-purpose cold plate for thermal applications such as TEC, LED, image sensor, and semiconductor cooling. The cooling area footprint is 45mm x 45mm (1.8in x 1.8in), and it utilizes a square peg array internal structure.


One loose steel bracket is included, designed for easy fabrication and modification (see dimensions under the "Files" tab). The included bracket accommodates diagonal mounting hole distances from approximately 67mm to 95mm (2.64in to 3.7in). The top two screws are for bracket orientation only, and may be removed from the cold plate to freely rotate the bracket.

Cold plate materials include copper, a brass top, anti-corrosive nickel plating, and EPDM o-ring. Threaded for G


1/4 BSPP fittings.




Cold Plates	
Flow Resistance @ 5LPM (10-13mm ID)	0.049kgf/cm <sup>2</sup> (0.7psi)
Thermal Resistance @ 5LPM (Approx.)	0.07° C/W
General	
Weight	0.50 lb (0.23 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25° C	10kgf/cm <sup>2</sup> (142.2psi)
Max Temperature Tolerance	100° C (212° F)
Wetted Materials	Nickel-Plated Copper, Nickel-Plated Brass, EPDM

PLT-UN45P




PLT-UN45P





△					
REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
REVISION					

NO.		DESCRIPTION			MATER'L		QUANTITY	REMARKS
 <b>KOOLANCE®</b>					UNIT	MM	ITEM PLT-UN45F	
					SCALE	N/S	TITLE	
DATE	BY	BY	BY	APPRO BY	3RD ANGLE		Ass'y	
	S.J.LEE				CODE NO.		DWG. NO.	PAGE