







Coolant fill port for configurations without reservoirs (T-line air bleeding), or for separately locating the fill port from the reservoir. Can also be used as a drain valve if positioned low in the system. G 1/4 BSPP fitting threading, with bore size of 18mm (0.7"). Nickel-plated brass.

| General | |
|--------------------------------|---------------------------|
| Weight | 0.06 lb (0.03 kg) |
| Fitting Thread | G 1/4 BSPP |
| Max Pressure Tolerance @ 25° C | 15kgf/cm2 (213.4psi) |
| Max Temperature Tolerance | 120° C (248° F) |
| Wetted Materials | Nickel-Plated Brass, EPDM |



SECTION VIEW

| | | | | | | | | | | | |
|---|--|-------------|----|----|----------|-----------|-----|--------------------|--|---------|--|
| | | | | | | | | | | | |
| NO. | | DESCRIPTION | | | | MATER'L | | QUANTITY | | REMARKS | |
|  | | | | | | UNIT | MM | PART NO. PRT-XGK | | | |
| | | | | | | SCALE | N/S | TITLE Ass'y | | | |
| DATE | | BY | BY | BY | APPRO BY | 3RD ANGLE | | | | | |
| APR.07.2022 | | S.J.LEE | | | | DWG. NO. | | ITEM | | | |
| | | | | | | | | | | | |