

CPU-330 Water Block (AMD/Intel Processor)






The rugged Koolance CPU-330 provides ultra low temperatures in single or multi-core configurations using a patented Koolance design. Please select the desired fitting type for this base model (it does not include fittings).

A back plate maximizes heat transfer with precision contact. The CPU-330 also features a universal mounting adapter and standard G 1/4 BSPP threading in 1/4in (6mm), 3/8in (10mm), and 1/2in (13mm) ID diameters. It supports most boards using the following processors:


- AMD AM2 + 939/940/754 processors (64, Opteron, X2, FX, Sempron)
- AMD "F" 1207 (Quad, Opteron, X2, FX)
- AMD "A" 462 (XP, Duron)
- Intel LGA775 (Quad, Core 2 Duo, Core Duo, Extreme, Pentium)
- Intel 478 (Pentium 4, D, EE, M, Celeron)
- Intel Xeon (603, 604, LGA771)

General	
Weight	1.25 lb (0.57 kg)
Wetted Materials	Gold-Plated Copper, Nickel-Plated Brass or Aluminum







Pressure Drop vs. Flow Rate




Thermal Resistance vs. Pressure Drop



Pressure Drop vs. Flow Rate



Thermal Resistance vs. Flow Rate



Thermal Resistance vs. Pressure Drop

