



Following the extremely successful CPU-350 comes Koolance's latest high-performance CPU water block. The CPU-360 uses an advanced microfin cold plate (0.25mm fins, 0.30mm channels), o-ring sealed impingement plate, and an optimized flow path to yield best performance with relatively low coolant restriction.

The CPU-360 contains a copper cold plate with brass top. As with all Koolance products, nickel plating is added to improve corrosion resistance. Two universal steel mounting brackets are included for mainstream Intel and AMD processors. The CPU-360 has standard G 1/4 BSPP threading for any Koolance fitting diameter. Please select the desired fitting type for this base model (it does not include fittings).

The CPU-360 supports most boards using the following processors:

- AMD socket AM2, AM2+, AM3
- AMD socket F/1207 (with separate [BKT-CP021K](#))
- AMD socket G34 (with separate [BLT-CPAMDG34](#))
- Intel socket LGA 1155/1156
- Intel socket LGA 1366
- Intel socket LGA 775

General	
Weight	0.80 lb (0.36 kg)
Materials	Nickel-Plated Copper, Nickel-Plated Brass, Stainless Steel, EPDM



